

| Material ID | Description | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|---------------------------|------------------|--------------|---------------|------------|---------------------|
| 01R2101 | IHQ Manager | | | | | |
| 01R2102 | IHQM Software | | | | | |
| 01R2103 | i-STAT Device Fee | | | | | |
| 01R2104 | IHQM HL7 R Int | | | | | |
| 01R2105 | IHQM ADT I Mod | | | | | |
| 01R2106 | IHQM STAT Note | | | | | |
| 01R2107 | IHQM Rem Imp Tra | | | | | |
| 01R2108 | IHQM On Imp Train | | | | | |
| 01R2109 | IHQM Software Patch | | | | | |
| 01R2110 | IHQM Software Upgrade | | | | | |
| 01R2111 | IHQM SW TEST SYS | | | | | |
| 01R2112 | IHQ CUSTOM INT | 0 | 0 | 0 | 0 | 0 |
| 01R2113 | IHQM DI ORDER INT | | | | | |
| 01R2114 | IHQM DI LMS INT | | | | | |
| 01R2115 | IHQM DEV CNCT 1 | | | | | |
| 01R2116 | IHQM DEV CNCT 10 | | | | | |
| 01R2117 | IHQM DI ASTM INT | | | | | |
| 01R2118 | IHQM Test Select Set | | | | | |
| 01R2119 | IHQM DI CART ADD | | | | | |
| 01R2120 | IHQM DI FCLTY ADD | | | | | |
| 01R2121 | IHQM Basic Connect | | | | | |
| 01R2123 | IHQM Premier Plus Connect | | | | | |
| 01R2124 | IHQM Platinum Connect | | | | | |
| 01R2126 | IHQM TST IST CT 10 | | | | | |
| 01R2127 | IHQM DI ADT INT | | | | | |
| 01R2128 | IHQM DITEST ORDINT | | | | | |
| 01R2129 | IHQM DI I-ST CT 10 | | | | | |
| 01R2130 | IHQM SQL 2-Core License | | | | | |
| 01R2134 | IHQM DI HL7 SETUP | | | | | |
| 01R2135 | IHQM DI ADT SETUP | | | | | |
| 01R2136 | IHQM DI STNT SETUP | | | | | |
| 01R2137 | IHQM DI TSTINT SET | | | | | |
| 01R2138 | IHQM DI ORDR SETUP | | | | | |
| 01R2139 | Info HQ Express | | | | | |
| 01R2140 | Info HQ Express Kit | | | | | |
| 01R2141 | IHQ Expr/DE Combo | | | | | |
| 01R2201 | i-STAT Device M | | | | | |
| 01R2202 | IHQM HL7 R I MA | | | | | |
| 01R2203 | IHQM ADT I MA | | | | | |
| 01R2204 | IHQM STAT N MA | | | | | |
| 01R2205 | IHQM DI TST MNTY1 | | | | | |
| 01R2208 | IHQM DI TSTADT MT1 | | | | | |

| Material ID | Description | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|----------------------------------|------------------|--------------|---------------|------------|---------------------|
| 01R2209 | IHQM ISTATCT MNT1 | | | | | |
| 01R2210 | IHQM 10DEVCT MNT1 | | | | | |
| 01R2211 | IHQM DI ASTM MNT1 | | | | | |
| 01R2221 | IHQM Basic Maintenance | | | | | |
| 01R2222 | IHQM Premier Maintenance | | | | | |
| 01R2223 | IHQM Premier Plus Maintenance | | | | | |
| 01R2224 | IHQM Platinum Maintenance | | | | | |
| 01R2225 | IHQM SW SYS KT MNT | | | | | |
| 01R2226 | IHQM DI HL7 MNT2 | | | | | |
| 01R2227 | IHQM DI TSTHL7 MT1 | | | | | |
| 01R2229 | IHQM DI TST10D MT1 | | | | | |
| 01R2230 | IHQM DITST10ISTMT1 | | | | | |
| 01R2231 | IHQM DI I-ST 10MNT | | | | | |
| 01R2232 | IHQM DI I-ST 10MT2 | | | | | |
| 01R2233 | IHQM DI ADT MNT2 | | | | | |
| 01R2234 | IHQM DI ORD MNT2 | | | | | |
| 01R2235 | IHQM AD HOC TRAINING | | | | | |
| 01R2236 | IHQM DI TSTHL7 MT2 | | | | | |
| 01R2237 | IHQM DI TST10D MT2 | | | | | |
| 01R2238 | IHQM DI TSTADT MT2 | | | | | |
| 01R2239 | IHQM DI TSTORD MT2 | | | | | |
| 01R2240 | IHQM DI ORDR MNT1 | | | | | |
| 01R2241 | IHQ EXP SVC 1YR | | | | | |
| 01R2242 | IHQ EXP SVC 2YR | | | | | |
| 01R2243 | IHQ EXP SVC 3YR | | | | | |
| 01R2244 | IHQ EXP SVC 4YR | | | | | |
| 01R2245 | IHQ EXP SVC 5YR | | | | | |
| 01R2246 | IHQ EXPwSVC 3YR | | | | | |
| 01R2247 | IHQ EXPwSVC 5YR | | | | | |
| 01R2251 | IHQEX+DE SVC 1YR | | | | | |
| 01R2252 | IHQEX+DE SVC 2YR | | | | | |
| 01R2253 | IHQEX+DE SVC 3YR | | | | | |
| 01R2254 | IHQEX+DE SVC 4YR | | | | | |
| 01R2255 | IHQEX+DE SVC 5YR | | | | | |
| 01R2256 | i-STAT Conn Kit, 3 YR | | | | | |
| 01R2257 | i-STAT Conn Kit, 5 YR | | | | | |
| 01R5325 | CART, PTH, CR1 | | | | | |
| 02R2901 | BHCG Control Lvl 1 | | | | | |
| 02R2902 | BHCG Control Lvl 2 | | | | | |
| 02R2903 | BHCG Control Level 3 | | | | | |
| 02R6001 | IST Model 500 Anz | | | | | |

| Material ID | Description | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|-----------------------------|------------------|--------------|---------------|------------|---------------------|
| 02R6101 | IST Base Station | | | | | |
| 02R6201 | IST E-Simulator | | | | | |
| 02R6301 | IST Model500RchBat | | | | | |
| 02R6401 | IST BS Power Spply | | | | | |
| 02R6405 | i-STAT/Alinity Pmtr Kit | | | | | |
| 02R6406 | BS, Power Cord, Japan | | | | | |
| 02R6410 | BS, Power Cord, USA | | | | | |
| 02R6411 | BS, Power Cord, UK | | | | | |
| 02R6412 | BS, Power Cord, Australia | | | | | |
| 02R6413 | BS, Power Cord, India, SA | | | | | |
| 02R6414 | BS, Power Cord, Netherlands | | | | | |
| 02R6415 | BS, Power Cord, Argentina | | | | | |
| 02R6416 | BS, Power Cord, China | | | | | |
| 02R6417 | BS, Power Cord, Israel | | | | | |
| 02R6418 | BS, Power Cord, Switzerland | | | | | |
| 02R6501 | IST Model500ManIUS | | | | | |
| 03P1201 | Unify HW/SW 1 Inst | | | | | |
| 03P1202 | Unify SW 1 Inst | | | | | |
| 03P1301 | Unify Drvr 1 Inst | | | | | |
| 03P1302 | Unfiy Serial Cbl | | | | | |
| 03P1303 | Unify Pwr Supply | | | | | |
| 03P1304 | Unify Pwr Cord | | | | | |
| 03P1305 | Unify USB Stick | | | | | |
| 03P1401 | Unify Addtl Setup | | | | | |
| 03P1402 | Non-SA PPI | | | | | |
| 03P1403 | Unify SA | | | | | |
| 03P1404 | Unify S&H | | | | | |
| 03P7501 | ISTAT1 WIRELESS(1) | | | | | |
| 03P7502 | ISTAT WIFI UG(1) | | | | | |
| 03P7506 | ISTAT WIRELESS WW | | | | | |
| 03P7512 | ISTAT WIFI UG UK | | | | | |
| 03P7513 | ISTAT WIFI UG GERMANY | | | | | |
| 03P7514 | ISTAT WIFI UG FRENCH | | | | | |
| 03P7515 | ISTAT WIFI UG SPANISH | | | | | |
| 03P7516 | ISTAT WIFI UG ITALIAN | | | | | |
| 03P7517 | ISTAT WIFI UG DUTCH | | | | | |
| 03P7518 | ISTAT WIFI UG SWEDISH | | | | | |
| 03P7520 | ISTAT WIFI UG DANISH | | | | | |

| Material ID | Description | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|-------------------------|------------------|--------------|---------------|------------|---------------------|
| 03P7521 | ISTAT WIFI UG CHINA | | | | | |
| 03P7522 | ISTAT WIFI UG NORWEGIAN | | | | | |
| 03P7523 | ISTAT WIFI UG FINNISH | | | | | |
| 03P7524 | ISTAT WIFI UG KOREAN | | | | | |
| 03P7550 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7551 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7552 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7553 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7554 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7555 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7556 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7599 | ISTAT WIRLES REFB(1) | | | | | |
| 03P7625 | APOC EG7+ CART(1X25) | | | | | |
| 03P7650 | CART, EG7+, CR1 | | | | | |
| 03P7725 | APOC EG6+ CART(1X25) | | | | | |
| 03P7850 | CART, G3+, CR1 | | | | | |
| 03P8025 | APOC 6+ CART(1X25) | | | | | |
| 03P8125 | APOC EC4+ CART | 0 | 0 | 0 | 0 | 0 |
| 03P8225 | APOC E3+ CART(1X25) | | | | | |
| 03P8425 | APOC CREA CART(1X25) | | | | | |
| 03P8450 | CART, CREA, CR1 | | | | | |
| 03P8525 | APOC CG4+ CART(1X25) | | | | | |
| 03P8550 | CART, CG4+, CR1 | | | | | |
| 03P8625 | APOC ACTC CART(1X25) | | | | | |
| 03P8725 | APOC ACTK CART | | | | | |
| 03P8825 | APOC CG8+ CART(1X25) | | | | | |
| 03P8850 | CART, CG8+, CR1 | | | | | |
| 03P9025 | APOC TROPONIN CAR(1X25) | | | | | |
| 03P9225 | APOC CK-MB CART(1X25) | | | | | |
| 03P9250 | CART, CKMB, CR1 | | | | | |
| 03P9325 | APOC BNP CART | | | | | |
| 03P9350 | CART, BNP, CR1 | | | | | |
| 03R1201 | Unify HW/SW 1 Inst | | | | | |
| 03R1202 | Unify SW 1 Inst | | | | | |
| 03R1301 | Unify Drvr 1 Inst | | | | | |
| 03R1302 | Unify Serial Cbl | | | | | |
| 03R1303 | Unify Pwr Supply | | | | | |
| 03R1304 | Unify Pwr Cord | | | | | |

| Material ID | Description | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|---------------------------------|------------------|--------------|---------------|------------|---------------------|
| 03R1305 | Unify USB Stick | | | | | |
| 03R1401 | Unify Addtl Setup | | | | | |
| 03R1402 | Non-SA PPI | | | | | |
| 03R1403 | Unify SA | | | | | |
| 03R1404 | Unify S&H | | | | | |
| 03R3901 | CD-ROM, Chinese I | | | | | |
| 04J4820 | IST1 GVTFIELDKIT(1EA) | | | | | |
| 04J4840 | Cool Box Kit | | | | | |
| 04J4850 | IST DISTRIB KIT(1EA) | | | | | |
| 04J4853 | DSTB KT w/3YR SRV | | | | | |
| 04J4855 | DSTB KT w/5YR SRV | | | | | |
| 04J5021 | IST PT LVL 1 CTL(10X1.7) | | | | | |
| 04J5022 | IST PT LVL 2 CTL(10X1.7) | | | | | |
| 04J6020 | IST WAIVED KIT(1) | | | | | |
| 04J6021 | WAVD KT w/3YR SRV | | | | | |
| 04J6025 | WAVD KT w/5YR SRV | | | | | |
| 04P7301 | IST DWNLDR RCGR(1) | | | | | |
| 04P7303 | IST DWNLDR CABLES(1) | | | | | |
| 04P7304 | IST DWNLDR RGR K | | | | | |
| 04P7305 | i-STAT 1 DLR, China | | | | | |
| 04P7402 | ISTAT COMBO PS(1) | | | | | |
| 04P7403 | STAT1 RECHRG BTRY | | | | | |
| 04P7404 | ISTAT PRINTER KIT(1) | | | | | |
| 04P7410 | Alinity Printer Kit, AUS, NZ | | | | | |
| 04P7411 | Alinity Printer Kit, EU | | | | | |
| 04P7412 | Alinity Printer Kit, SA | | | | | |
| 04P7413 | Alinity Printer Kit, UK | | | | | |
| 04P7501 | IST STAT 1 ANALYZ | | | | | |
| 04P7502 | i-STAT 1 Analyzer, China | | | | | |
| 04P7530 | i-STAT 1 Analyzer 30R | | | | | |
| 04P7531 | i-STAT 1 Analyzer 31R | | | | | |
| 04P7532 | i-STAT 1 Analyzer 32R | | | | | |
| 04P7802 | IST1 WRLS CDROM 2(1) | | | | | |
| 04P7803 | IST1 WRLS CDROM 3 | | | | | |
| 05P0108 | ISLS STARTER KIT(1) | | | | | |
| 05P5825 | APOC BHCG CART(1X25) | | | | | |
| 05P5901 | BHCG CONTROL LV1(1) | | | | | |
| 05P5902 | BHCG CONTROL LV2(1) | | | | | |
| 05P5903 | BHCG CONTROL | | | | | |

| Material ID | Description | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|-------------------------------|------------------|--------------|---------------|------------|---------------------|
| | LV3(1) | | | | | |
| 05P5904 | BHCG CAL VER(1) | | | | | |
| 05P7001 | TRICONTRL CALVER(1) | | | | | |
| 05P7101 | TRICONTRL LVL 1(1) | | | | | |
| 05P7201 | TRICONTRL LVL 2(1) | | | | | |
| 05P7301 | TRICONTRL LVL 3(1) | | | | | |
| 05P7515 | Alinity Latch Return Tool | | | | | |
| 06F1101 | IST ELEC SIMULATR | | | | | |
| 06F1102 | i-STAT 1 Sim, China | | | | | |
| 06F1201 | IST LVL1 AQUUS CTL(10X1.7) | | | | | |
| 06F1202 | IST TRPN CTL LVL1(1X6BTL) | 0 | 0 | 0 | 0 | 0 |
| 06F1204 | IST HCT LVL 1 CNT(1BX) | 0 | 0 | 0 | 0 | 0 |
| 06F1205 | IST HCT LVL 2 CNL(1) | | | | | |
| 06F1206 | IST HCT LVL 3 CNT | | | | | |
| 06F1207 | IST HCT CAL VERF(1) | | | | | |
| 06F1209 | IST CKMB LVL 1 C(1BX) | 0 | 0 | 0 | 0 | 0 |
| 06F1210 | IST CKMB LVL2 C(1BX) | 0 | 0 | 0 | 0 | 0 |
| 06F1211 | IST CKMB LVL3 C(1BX) | 0 | 0 | 0 | 0 | 0 |
| 06F1212 | IST CKMB TRILVL C(1BX) | 0 | 0 | 0 | 0 | 0 |
| 06F1213 | IST CHEM8 LVL1 C(1BX) | | | | | |
| 06F1214 | IST CHEM8 LVL1B C(1BX) | | | | | |
| 06F1215 | IST CHEM8 LVL2 C(1BX) | | | | | |
| 06F1216 | IST CHEM8 LVL3 C(1BX) | | | | | |
| 06F1217 | IST CHEM8 CAL VER(1BX) | | | | | |
| 06F1218 | IST BNP LVL 1 C(1 BX) | 0 | 0 | 0 | 0 | 0 |
| 06F1219 | IST BNP LVL 2 C(1BX) | 0 | 0 | 0 | 0 | 0 |
| 06F1220 | IST BNP LVL 3 C(1 BX) | 0 | 0 | 0 | 0 | 0 |
| 06F1221 | IST BNP CAL VERF(1 BX) | 0 | 0 | 0 | 0 | 0 |
| 06F1301 | IST LVL2 AQUUS CTL | | | | | |
| 06F1302 | IST TRPN CTL LVL2(1X6BTL) | 0 | 0 | 0 | 0 | 0 |
| 06F1401 | IST LVL3 AQUUS CTL(10X1.7) | | | | | |
| 06F1402 | IST TRPN CTL LVL3(1X6BTL) | 0 | 0 | 0 | 0 | 0 |
| 06F1501 | IST CAL VER(20X1.7) | | | | | |
| 06F1502 | IST TRPN CAL V/KT(1X6BTL) | 0 | 0 | 0 | 0 | 0 |
| 06F1630 | STAT1 OP/MNL US(1) | | | | | |

| Material ID | Description EA) | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|---------------------------------|------------------|--------------|---------------|------------|---------------------|
| 06F1635 | ISTAT1 OP/MNL ITLN | | | | | |
| 06F1639 | STAT1 PWR CRD US(1EA) | | | | | |
| 06F1643 | STAT1 PWR CRD UK | 0 | 0 | 0 | 0 | 0 |
| 06F1679 | IST 1 GVT HS CASE(1EA) | | | | | |
| 06F1682 | DL/PR PWR Cable, Argentina | | | | | |
| 06F1683 | DL/PR PWR Cable, China | | | | | |
| 06F1684 | DL/PR PWR Cable, Israel | | | | | |
| 06F1685 | DL/PR PWR Cable, Switzerland | | | | | |
| 06F1687 | IST1 USER GD Czech | | | | | |
| 06F1688 | IST1 USER GD Slovakian | | | | | |
| 06F1689 | IST1 USER GD Polish | | | | | |
| 06F1690 | IST1 USER GD Russian | | | | | |
| 06F1691 | IST1 USER GD Romanian | | | | | |
| 06F1692 | IST1 USER GD Finnish | | | | | |
| 06F1697 | DL/PR PWR Cable, Japan | | | | | |
| 06F1710 | PRINTER CRADLE(1 EA) | | | | | |
| 06F1711 | PORT PRNTR PAPER(1X6) | | | | | |
| 06F1910 | SEIK PRNTR PAPER(1 ROLL) | | | | | |
| 06F2003 | IST WAIVED TEST M(1) | | | | | |
| 06F2020 | IST WAIVED ANALY(1) | | | | | |
| 06F2023 | WAVD AL KT w/3YRSRV | | | | | |
| 06F2025 | WAVD AL KT w/5YRSRV | | | | | |
| 06F2113 | IR LINK CABLE(2 FT) | | | | | |
| 06F2114 | IR LINK CABLE(5 FT) | | | | | |
| 06F2126 | 9V LITHIUM BATTYS(1X6) | | | | | |
| 06F2132 | 8.4V Recharge Battery | | | | | |
| 06F2133 | Powerex Batt Charger | | | | | |
| 06F2135 | IST PRNTR BATTERY(1) | | | | | |
| 06F2136 | Battery Carrier Assy | | | | | |
| 06F2137 | Battery Door Assy | | | | | |
| 06F2138 | Foot Housing, 4pcs Kit | | | | | |
| 06F2139 | Ceramic Cart Strip, REPL | | | | | |
| 06F2355 | IST RCHRGBL BTRY(1EA) | | | | | |

| Material ID | Description | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|---------------------------------------|------------------|--------------|---------------|------------|---------------------|
| 06F2357 | DOWNLOADRECHR GCX(1X1) | | | | | |
| 06F2360 | IST CDS V5.0(EACH) | | | | | |
| 06F2363 | DL LAN FILTER CBL(1) | | | | | |
| 06F2401 | IST MDL1 LIS I/FC(EACH) | | | | | |
| 06F2416 | ISTAT DISPENSING(1B/500) | | | | | |
| 06F2420 | Dispensing Tip 100pk | | | | | |
| 06F2430 | Dispensing Tip 500pk | 0 | 0 | 0 | 0 | 0 |
| 06F2450 | Closed Transfer Device | | | | | |
| 06P1701 | CKMB CTRL LV 1(1) | | | | | |
| 06P1702 | CKMB CTRL LV 2(1) | | | | | |
| 06P1703 | CKMB CTRL LV 3(1) | | | | | |
| 06P1704 | CKMB CAL VER(1) | | | | | |
| 06P1705 | BNP CTRL LV 1(1) | | | | | |
| 06P1706 | BNP CTRL LV 2(1) | | | | | |
| 06P1707 | BNP CTRL LV 3(1) | | | | | |
| 06P1708 | BNP CAL VER(1) | | | | | |
| 06P1709 | TROPONIN CTL LV 1 | | | | | |
| 06P1710 | TROPONIN CTL LV 2(1) | | | | | |
| 06P1711 | TROPONIN CTL LV 3(1) | | | | | |
| 06P1712 | TROPONIN CAL VER(1) | | | | | |
| 06P1713 | PT CTL LV 1(1) | | | | | |
| 06P1714 | PT CTL LV 2(1) | 0 | 0 | 0 | 0 | 0 |
| 06P1715 | ACT CTL LV 1 | | | | | |
| 06P1716 | ACT CTL LV 2 | | | | | |
| 06P2325 | APOC Troponin Cart | 0 | 0 | 0 | 0 | 0 |
| 06P2801 | Contact Pin Cleaning Kit | | | | | |
| 07G8201 | IST LVL1 ACT CTL(10X1.7) | 0 | 0 | 0 | 0 | 0 |
| 07G8301 | ISTA LVL2 ACT CTL(10X1.7) | 0 | 0 | 0 | 0 | 0 |
| 07P0405 | Piccolo Waived Comp Binder Assy | | | | | |
| 07P0406 | Piccolo Mod Complexity Comp Binder | | | | | |
| 07P0407 | Piccolo Paper Roll (Box of 6) | | | | | |
| 07P0408 | Piccolo Express Ops Manual | | | | | |
| 07P0409 | Piccolo Fan Filter 60MM | | | | | |
| 07P0410 | Piccolo Fan Filter 80MM | | | | | |
| 07P0411 | Piccolo IRIS Power Supply | | | | | |
| 07P0412 | Piccolo VS2 Power Inverter | | | | | |
| 07P0413 | Piccolo Result Cards, | | | | | |

| Material ID | Description | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|--|------------------|--------------|---------------|------------|---------------------|
| | 300 PK | | | | | |
| 07P0414 | Piccolo Lith Heparin Microtainer 3ml | | | | | |
| 07P0415 | Piccolo Minipet,100UL Gray | | | | | |
| 07P0416 | Piccolo Tip,Disp,Rach of 96 | | | | | |
| 07P0417 | Piccolo LIPD Int'l Guide | | | | | |
| 07P0418 | Piccolo Power Cord,Black Jacket | | | | | |
| 07P0420 | Piccolo Gov Field Expres Deply Case | | | | | |
| 07P0501 | Piccolo Express Analyzer | | | | | |
| 07P0502 | Piccolo Government Field Kit | | | | | |
| 08K4601 | ISTAT DE SFTWR(EACH) | | | | | |
| 08K4620 | ISTAT DE SW HOSP LIC | | | | | |
| 08K4621 | ISTAT DE SW POL LIC | | | | | |
| 09P3125 | APOC CHEM8 CART(1X25) | | | | | |
| 09P3720 | ALINITY I DHEAS RGT (200T) | | | | | |
| 09P3721 | ALINITY I DHEAS RGT (1000T) | | | | | |
| 09P8125 | CART, cTnl NxG | | | | | |
| 02R6002 | Alinity Analyzer R&R | | | | | |
| 02R6082 | Alinity Analyzer 82R | | | | | |
| 06F1693 | IST1 USER GD TW & KR | | | | | |
| 02R6080 | Alinity Analyzer 80R | | | | | |
| 02R6081 | Alinity Analyzer 81R | | | | | |
| 02R6421 | BS, Power Cord, Taiwan | | | | | |
| 02R6422 | DL/PR Power Cord, Brazil | | | | | |
| 02R6420 | BS, Power Cord, Philippines | | | | | |
| 02R6419 | BS, Power Cord, Brazil | | | | | |
| 07P0201 | Piccolo Gen'l Chem 6 (Box of 10) | | | | | |
| 07P0202 | Piccolo Electrolyte Panel (Box of 10) | | | | | |
| 07P0205 | Piccolo LIPID Panel (Box of 10) | | | | | |
| 07P0203 | Piccolo Metlyte 8 Panel (Box of 10) | | | | | |
| 07P0204 | Piccolo Basic Metabolic Panel(Box of 10) | | | | | |
| 07P0206 | Piccolo Hepatic Panel (Box of 10) | | | | | |
| 07P0208 | Piccolo Comp.Metabolic Panel (Box of 10) | | | | | |

| Material ID | Description | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|---|------------------|--------------|---------------|------------|---------------------|
| 07P0210 | Piccolo Liver Panel Plus (Box of 10) | | | | | |
| 07P0207 | Piccolo Renal Panel (Box of 10) | | | | | |
| 07P0209 | Piccolo Kidney check (Box of 10) | | | | | |
| 07P0215 | Piccolo Biochem Panel Plus (Box of 10) | | | | | |
| 07P0213 | Piccolo Basic Meta Plus (Box of 10) | | | | | |
| 07P0211 | Piccolo Gen'l Chemistry 13 (Box of 10) | | | | | |
| 07P0212 | Piccolo LIPID Panel Plus (Box of 10) | | | | | |
| 07P0214 | Piccolo Metlyte Plus CRP (Box of 10) | | | | | |
| 07P0403 | Piccolo Verification Controls | | | | | |
| 07P0404 | Piccolo Verification Samples w/CRP | | | | | |
| 07P0216 | Piccolo MetLac 12 Panel | | | | | |
| 07P0402 | Piccolo Chem Contrl w/CRP | | | | | |
| 07P0401 | Piccolo Lipid & Gen'l Chem Contrl | | | | | |
| 07P0419 | Piccolo Gov Field Xpres Dspy Kit | | | | | |
| 03P7557 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7561 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7559 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7558 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7562 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7563 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7560 | i-STAT1WrIsAnzUpgd | | | | | |
| 01R2207 | IHQM DI ORDR MNT1 | | | | | |
| 06P1717 | PTplus/aPTT Control L1 | | | | | |
| 06P1719 | PTplus/aPTT Control L3 | | | | | |
| 02R6104 | i-STAT Alinity Charge Station | | | | | |
| 03P8951 | PTplus/aPTT Cartridge | | | | | |
| 03P8950 | PTplus Cartridge | | | | | |
| 03P7580 | iSTAT Wireless Upg w/2yrServ | | | | | |
| 03P7570 | iSTAT Wireless Anl w/2yr Serv | | | | | |
| 04P7550 | i-STAT 1 Analyzer w/2yr Serv | | | | | |
| 06P1723 | i-STAT Tnl-Nx Control L3 | | | | | |
| 06P1722 | i-STAT Tnl-Nx Control L2 | | | | | |
| 06P1721 | i-STAT Tnl-Nx Control L1 | | | | | |

| Material ID | Description | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|---------------------------------------|------------------|--------------|---------------|------------|---------------------|
| 06P1720 | i-STAT Tnl-Nx Cal Ver Set | | | | | |
| 06P1724 | i-STAT TBI Cal Ver Set | | | | | |
| 06P1726 | i-STAT TBI Control L2 | | | | | |
| 06P1725 | i-STAT TBI Control L1 | | | | | |
| 07P0551 | Piccolo Anl w/5yr Serv | | | | | |
| 07P0550 | Piccolo Anl w/3yr Serv | | | | | |
| 02R6424 | BS, Power Cord, Nepal | | | | | |
| 02R6425 | DL/PR PWR Cable, Nepal | | | | | |
| 02R6423 | BS, Power Cord, Senegal | | | | | |
| 04W5325 | Tnl-NX Cartridge | | | | | |
| 04P7405 | i-STAT1 Printer, China | | | | | |
| 06F1694 | IST1 USER GD HU | | | | | |
| 04X6425 | i-STAT TBI PLASMA CARTRIDGE | | | | | |
| 03P7595 | iSTAT1 Wireless Analyzer 5ghz upgrade | | | | | |
| 03P7507 | ISTAT WIRELESS ANZ 5ghz | | | | | |
| 03P7597 | iSTAT1 Wireless ANZ 5ghz upgrade | | | | | |
| 09P3126 | APOC CHEM8 CART(1X25) | 0 | 0 | 0 | 0 | 0 |
| 03P7582 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7585 | i-STAT1WrIsAnzUpgd | | | | | |
| 03P7584 | i-STAT1WrIsAnz5ghz | | | | | |
| 03P7583 | iSTAT1 Wireless Analyzer 5ghz | | | | | |
| 03P7581 | iSTAT1 Wireless Analyzer 5ghz | | | | | |
| 03P7586 | iSTAT1 Wireless Analyzer 5ghz | | | | | |
| 03P7591 | iSTAT1 Wireless Analyzer 5ghz | | | | | |
| 03P7590 | iSTAT1 Wireless Analyzer 5ghz | | | | | |
| 03P7589 | iSTAT1 Wireless Analyzer 5ghz | | | | | |
| 03P7588 | iSTAT1 Wireless Analyzer 5ghz | | | | | |
| 03P7587 | iSTAT1 Wireless Analyzer 5ghz | | | | | |
| 03P7592 | iSTAT1 Wireless Analyzer 5ghz | | | | | |
| 04P7503 | IST STAT 1 ANALYZ | | | | | |
| 03P8551 | CART, CG4+, CR1 | | | | | |
| 06F1718 | PTplus/aPTT Control L2 | | | | | |
| 03S1001 | ID NOW INSTRUMENT | | | | | |
| 03S1101 | ID NOW COVID19 KITS 24T | | | | | |
| 06F2358 | IST RCHRGBL | | | | | |

| Material ID | Description | Product Category | Package Size | Saleable Unit | Instrument | Basic Configuration |
|-------------|---|------------------|--------------|---------------|------------|---------------------|
| | BTRY(1EA) CHINA | | | | | |
| 01R2171 | INFOHQ SW+DE Kit | | | | | |
| 01R2170 | Info HQ SW Kit | | | | | |
| 03P5850 | CART, B-hCG, CR1 | | | | | |
| 06S9401 | i-STAT1 WL ANZ w/ 3YR SRV | | | | | |
| 06S9403 | i-STAT1 ANZ UP w/ 3YR SRV | | | | | |
| 06S9404 | i-STAT1 ANZ w/ 3YR SRV | | | | | |
| 06S9402 | i-STAT1 WL UP w/ 3YR SRV | | | | | |
| 02R6005 | Alinity System Kit | | | | | |
| 04P7406 | iStat1 Printer Rechargeable Battery CN | | | | | |
| 04P734R | IST DWNLDR RGA Repair | | | | | |
| 06S9411 | i-STAT1 WIRELESS DISTRIB KIT | | | | | |
| 06S9412 | i-STAT1 WIRELESS DISTRIB KIT w/ 3YR SRV | | | | | |
| 06S9410 | i-STAT1 5GHZ WIRELESS ANZ w/ 5YR SRV | | | | | |
| 06S9415 | i-STAT1 WIRELESS EMR KIT | | | | | |
| 06S9413 | i-STAT1 WIRELESS DISTRIB KIT w/ 5YR SRV | | | | | |
| 06S9414 | i-STAT1 WIRELESS DISTRB SFTWRE | | | | | |
| 06S9416 | i-STAT1 WIRELESS EMR KIT w/ 3YR SRV | | | | | |
| 06S9417 | i-STAT1 WIRELESS EMR KIT w/ 5YR SRV | | | | | |
| 06U8713 | ADD SIMULATOR | | | | | |
| 03P7826 | G3+ Cartridge | | | | | |
| 03P8326 | Glucose Cartridge | | | | | |
| 06P1718 | PTplus/aPTT Control L2 | | | | | |
| 03S0925 | TBI Whole Blood Cartridge | | | | | |